### Quick Start Guide





Saga 7" Super High Bright 3G-SDI/HDMI Touchscreen Monitor with 3D LUTs and Scopes Deluxe Kit



6

J

You

 $\bigcirc$ 

### What's Included

- 1 x S7P Monitor
- 1 x Power Adapter
- 1 x Shoe Mount
- 1 x Soft Carry Case
- 1 x Slim HDMI Cable (Mini to Standard)
- 1 x Slim HDMI Cable (Micro to Standard)
- 1 x Slim SDI Cable
- 2 x IBS-550 Battery
- 1 x Battery Charger

# **Getting Started**

- 1. Menu Button Scroll Wheel Used to enter and navigate the menu
- 2. Exit / Back Used to exit or go back
- 3. Mute Toggle sound on and off
- 4. Source

Switch between SDI and HDMI inputs

- 5. 1/4"-20 Threaded Mounting Points
- 6. Power Button Hold 3 seconds to turn on/off
- 7. DC 7-24V Power Terminal
- 8. SDI Input Terminal
- 9. SDI Output Terminal

- 10. SD Card Slot Used to load LUTs
- 11. 3.5mm Headphone Output
- 12. HDMI Input Terminal
- 13. HDMI Output Terminal
- 14. L Series Battery Slots Option to use 1 or 2 DV batteries



### Assist Menu Dropdown

Assist	$\sim$	]								
• Monochrome			Monoch	rome	— Togg	le be	etween of	ff, gra	y, red, g	preen, a
False Color			off		gray		red		green	
Peak Color			blue							
TC Timecode										
Zebra										
💫 Mute			False Co	lor —	- Two typ	oes d	of visual e	expos	ure ima	ge ovel
Nine Grid			off		type 1		type 2			
Mark		Ì						_		
Image Setting										
Color Setting		G	Peak Co	lor —	Activate	e pea	aking in s	select	color	
Signal Analysis			off		red	ר	green		blue	
System		l					-			
			Zebra —	- Use	75IRE or 75IRE	- 100	DIRE to cl	heck e	exposure	9
		¥2	Mute —	· Toggi	le sound	on/c				
			Nine Gri	d — 2	Zoom in	on o	ne of the	9 se	ctions	

Ð

Ø

 $\mathbf{O}$ 

You

Assist	
Mark	<
+ Center Mark	
⊆ ] Safety Marker	
回 Guide	
🗖 Guide Back	
📼 Marker Color	
₩ Grid Line	
Image Setting	>
Color Setting	>
Signal Analysis	
System	$\langle$

#### Mark Menu Dropdown

+ Center Mark — Toggle center crosshair on/off

### $+ \bigcirc$

**Safety Marker** — Select action area and title safe areas displayed

off	70%	80%	90%
16:9	16:10	4:3	5:4
1.85:1	2.35:1		

#### Guide — Apply aspect ratio frame guides



Guide Back — Option black out or half tone the areas outside of frame guides

large

You

U

 $\bigcirc$ 

half tone

off black

Marker Color — Pick marker line color

gray	yellow	red	green
blue	white	black	

**# Grid** — Apply grid lines to assist with composure



0

Acciet	~	III Video Aspect — Adjust video aspect ratio
Mark		auto 16:9 16:10 4:3
Image Setting	~	5:4 1.85:1 2.35:1 Stretch
III Video Aspect		
		□- Pixel to Pixel — Toggle on/off
I Zoom		
Zoom Times		
🔶 Flip		
Treeze		
Battery Level		
horHDR		
LUTLUI		4X 5X 6X 7X
Color Setting		8X 9X 10X user
Signal Analysis		
System		Ten Zoom Times — Adjust zoom by percentage
		<ul> <li>← Flip — Flip image</li> <li>off on auto</li> <li>① Freeze — Freeze frame</li> <li>①</li> </ul>
		Battery Level — Toggle Battery Level icon on/off
		High HDR - Preview HLG 2020, HLG 709, or HLG P3
		Off HLG 2020 HLG 709 HLG P3
		LUT — Toggle 3D LUTs on/off; import 3D LUTs from SD Ca
		SLOG2
		SLOG3

Ð

Ø

You

 $\mathbf{O}$ 

Image Setting Menu Dropdown

Appint		Ø Brightness
ASSISL		
Mark		- 0 - 50 - 50
Image Setting		
Color Setting	$\sim$	Q. Queden et
€ Brightness		U Contrast
Contrast		
<ul> <li>Saturation</li> </ul>		
Sharpness		
[] Colortemp		Saturation
Signal Analysis	~	
Svstem		50
,		
		Sharpness
		<b>_</b> _
		U Colortemp
		USER
		6500K
		9300K

### **Color Setting Menu Dropdown**

### Signl Analysis Menu Dropdown



# **Specifications**

Aspect Ratio	16:10
Battery	L Series Battery
Brightness	2000 nits
Contrast Ratio	1100:1
Inputs	1 x HDMI 1 x 3G-SDI 1 x 3.5mm Audio
Outputs	1 x HDMI 1 x 3G-SDI
Resolution	1920 x 1200
UPC Code	847983030736
Viewing Angle	178° (89°/89°)

# Supported Video Signals Specifications

HDMI	720x480i & 720x480p @ 59.94, 60 Hz 720x576i & 720x576p @ 50 Hz 1280x720p @ 50, 59.94, 60 Hz 1920x1080i @ 50, 59.94, 60 Hz 1920x1080psf @ 24, 25, 29.97, 30 Hz 1920x1080p @ 23.97, 24, 25, 29.94, 30, 50, 59.94, 60 Hz 3840x2160p @ 24, 25, 30 Hz 4096x2160p @ 24 Hz
3G-SDI	720x480i @ 59.94, 60 Hz 720x576i & 720*576p @ 50 Hz 1280x720p @ 50, 60 Hz 1920x1080i @ 50, 59.94, 60 Hz 1920x1080psf @ 24, 25, 29.97, 30 Hz 1920x1080p @ 23.93, 24, 25, 29.97, 30, 50, 59.94, 60 Hz

## **Optional Accessories**

Some other products that work well with this item available from Ikan include:

Ø

J

You

 $\mathbf{O}$ 

MA207	7 in. Articulating Arm
MA211	11 in. Articulating Arm
MA211-R	11 in. Articulating Arm w/ Single Rod Mount
IBS-750	IBS Sony L-Series NP-F750 Compatible Battery
IBS-970	IBS Sony L-Series NP-F970 Compatible Battery

## Learn More

More dynamic information at official website: www.ikancorp.com

# Support

Contact email: support@ikancorp.com

#### CONDITIONS OF WARRANTY SERVICE

- Free service for one year from the day of purchase if the problem is caused by manufacturing errors.
- The components and maintenance service fee will be charged if the warranty period is expired.

#### Free Service will not be provided in the following situations: (\*Even if the product is still within the warranty period.)

- Damage caused by abuse or misuse, dismantling, or changes to the product not made by the company.
- Damage caused by natural disaster, abnormal voltage, and environmental factors, etc.

©2019 Ikan International. All rights reserved.

0

67

 $\mathbf{ }$